



## "Under the Counter" Loop Kit

Our "Under the Counter" loop kit provides clear communication with hearing aid wearers, especially where high background noise is a problem or clear speech is restricted.

It has a flexible aerial that can be bent to shape, allowing it to be installed into many different positions.

The kit includes our halo indicator noise cancelling microphone as standard for high performance and self-testing. Our small omni-directional mouse microphone is also compatible with this system.

### Components

- Our new HLD2 driver
- Our noise cancelling halo indicator microphone
- The hearing loop aerial
- Power supply
- Fixings
- Signage

### Standards

- CE, ROHS and WEEE compliant
- BS EN 60118-4, in correct installations

### Physical Data (boxed)

Dimensions	Height – 85mm (3.15") Width – 320mm (12.6") Depth – 220mm (8.66")
Weight	0.8kg (1.76lbs)

### Applications

For use in any situation where one to one communication takes place at a counter, booth or desk, such as in:

- Banks
- Post offices
- Supermarkets
- Theatres
- Information centres
- Airports

### Features

Our 1 to 1 loop driver has the following features:

- Microprocessor control
- Energy-saving "green" standby mode is achieving a power saving of up to 80% during quiet periods
- Advanced audio processing features AGC, compression, and noise gate
- Constant-current loop drive
- Continuous self-testing
- Isolated audio line input allows the driver to take alternative audio sources (optional)
- Power and LED status indication

Talk to us now:

+44 (0) 1732 223900 (UK & ROW)

+1 616 392 3400 (US & Canada)

[www.contacta.co.uk](http://www.contacta.co.uk)



## Physical Data

Dimensions	Height - 116mm (4.57") Width - 116.2mm (4.58") Depth - 40mm (1.57")
Weight	300g (1.76lbs)
Construction	ABS Plastic Construction Housing
Finish	Matt Black, Fine Texture

## Technical Data

Inputs	Input 1 (Microphone)	Screw terminals on 3.8mm 2 pole Phoenix connector. Single-ended electret microphone, powered by 5V via 2.2K ohms
	Input 2 (Line) (Optional)	Screw terminals on 3.8mm 2 pole Phoenix connector. Transformer isolated, 0dBu into 1K ohms, may have series resistance added for optional 75V or 100V line inputs
	Power	Centre positive power jack, 14V DC 2A via 2.1mm from our P55 power supply unit
Loop output	Loop connection	Screw terminals on 3.8mm 2 pole Phoenix connector
Audio	Loop drive current	2A RMS compliance current @ 1Khz sine wave
	Loop drive voltage	4V RMS compliance voltage @ 1KHz sine wave
	Frequency response	100 Hz – 5kHz (±3dB)
	Distortion	Better than -40dB, inputs at nominal level
Automatic gain control	Processor controlled	Dynamic range: 40dB typical Attack time: 10 milliseconds Release time: typically 10 seconds, varies with program content
Indications	Status LEDs	3 colour LEDs indicate power, input and output diagnostic information Connection provided for our LED halo indicator microphone
Self Test	Microprocessor controlled	Unit, including microphone and loop connections is continuously monitored, and internal and external LED indicators are updated
Energy saving	Sound activated	Unit will enter low energy "sleep" mode when acoustic conditions indicate lack of usage

## Microphone Options



Noise cancelling halo indicator microphone



Mouse microphone